

HIGH SPEED STEELS

Application Segments

Cutting Tools	Automotive
---------------	------------

Available Product Variants

Long Products*	Plates

Product Description

BÖHLER \$390 MICROCLEAN - "The decathlete"

This grade is our PM steel with many positive usage properties. For twist drills, taps, mills, broaches, or cold-work applications, BÖHLER S390 MICROCLEAN is always a high performer.

Process Melting

Powder metallurgy

Properties

- > Toughness & Ductility : high
- > Wear Resistance : high
- > Compressive strength : very high
- > Edge Stability : very high
- > Grindability : high
- > Hot Hardness (red hardness) : very high

Applications

- > Motorsport industry
- > End Mills
- > Powder Pressing> Special Cutting Tools
- > Pill punching dies
- > Broaches and Reamers
- > Fine Blanking, Stamping, Blanking
- > Rolling
- > Twist Drills and Taps

- Cold Forming / Coining
- > Gear Cutting, Shaving and Shaping Tools
- > Shearing / Machine Knives
- > Wear parts

Chemical composition (wt. %)

С	Cr	Мо	V	W	Со
1.64	4.80	2.00	4.80	10.40	8.00



^{*} Presented data refer exclusivly to long products. Please observe the detailed explanations at the end of the data sheet (pdf).





Material characteristics

	Compressive strength	Grindability	Red hardness	Toughness	Wear resistance	Edge Stability
BÖHLER \$390 MICROCLEAN	***	***	***	***	***	***
BÖHLER \$290 MICROCLEAN	****	*	***	**	****	***
BÖHLER \$393 MICROCLEAN	***	***	***	***	***	***
BÖHLER \$590 MICROCLEAN	***	***	***	***	***	***
BÖHLER S690 MICROCLEAN	***	***	**	****	***	**
BÖHLER S790 MICROCLEAN	***	***	**	***	**	***
BÖHLER S793 MICROCLEAN	***	***	***	***	***	***

Delivery condition

Annealed				
Hardness (HB) max. 320 drawn execution max. 320 HB				
Tensile Strength (MPa ksi) max. 1,080 157				
Hardened and Tempered				
Hardness (HRC)	64 to 68			

Heat treatment

Annealing					
Temperature	770 to 840 °C 1,418 to 1,544 °F	4 h controlled slow cooling in furnace (10 to 20°C/h / (50 to 68°F/h) to 740°C/2h (1364°F/2 h) cooling in furnace,			
Otros e mellos dos s					
Stress relieving					
Temperature	600 to 650 °C 1,112 to 1,202 °F	Slow cooling in furnace. To relieve stresses set up by extensive machining or in tools of intricate shape. After through heating, hold in neutral atmosphere for 1 to 2 hours.			
Hardening and Tempering					
Temperature	1,100 to 1,230 °C 2,012 to 2,246 °F	Salt bath, vacuum Preheating: 1st stage $\sim 500~^\circ\text{C}$ (930 $^\circ\text{F}$), 2nd stage $\sim 850~^\circ\text{C}$ (1560 $^\circ\text{F}$), 3rd stage $\sim 1050~^\circ\text{C}$ (1920 $^\circ\text{F}$) Austenitising: 1100 - 1230 $^\circ\text{C}$ (2012 $^\circ\text{F}$ - 2246 $^\circ\text{F}$), holding time after complete heating 80 seconds, maximum 150 seconds, to avoid material damage due to overheating. Quenching: oil, warm bath (500 - 550 $^\circ\text{C}$ (930 $^\circ\text{F}$ - 1020 $^\circ\text{F}$)), gas			
Temperature	550 to 570 °C 1,022 to 1,058 °F	Slow heating to tempering temperature immediately after austenitising. Holding time in the furnace at least 2 hours Slow cooling to room temperature between each tempering step 3 tempering cycles recommended Hardness see tempering chart			






Continuous cooling CCT curves



Austenitising temperature: 1230°C (2246°F)

Holding time: 180 seconds



Austenitising temperature: 1230 °C (2246 °F)

Holding time: 180 seconds

O Vickers hardness

3...93 phase percentages

0.30...180 cooling parameter $\lambda,$ i.e. duration of cooling from 800 to 500 °C (1472 to 932 °F) in s x $10^{\text{-2}}$

A... Austenite

K... Carbide

P... Perlite

B... Bainite

M... Martensite

Ms... Martensite starting temperature


Quantitative phase diagram

Austenitisierungstemperatur: 1230°C

Haltedauer: 180 Sekunden

Austenitising temperature: 1230°C (2246°F)

Holding time: 180 seconds




- A....Austenite
- B....Bainite
- K....Carbide
- P....Perlite
- RA...Retained Austenite
- 1....Edge or Face

M....Martensite

- 2....Core
- 3....Jominy test: distance from quenched end
- watercooling
- -- oilcooling
- · aircooling



Tempering Chart



Holdingtime 3x2 hours

Specimensize: square 25mm

Austenitising in vacuum

Physical Properties

Temperature (°C °F)	20 68
Density (kg/dm³ lb/in³)	8.1 0.29
Thermal conductivity (W/(m.K) BTU/ft h °F)	17 9.82
Specific heat (kJ/kg K BTU/lb °F)	0.42 0.1003
Spec. electrical resistance (Ohm.mm²/m 10 ⁻⁴ Ohm.inch²/ft)	0.61 2.88
Modulus of elasticity (10³N/mm² 10³ksi)	231 33.5

Thermal Expansions between 20°C | 68°F and ...

Temperature (°C °F)	100	200	300	400	500	600	700
	212	392	572	752	932	1,112	1,292
Thermal expansion (10 ⁻⁶ m/(m.K) 10 ⁻⁶ inch/inch.°F)	10	10.5	10.8	11.2	11.3	11.4	11.6
	5.6	5.8	6	6.2	6.3	6.3	6.4

If other available product variants are listed in addition to long products, please note that these may differ in terms of melting process, technical data, delivery and surface condition as well as available product dimensions. For mandatory technical specifications, other requirements and dimensions, please contact our regional voestalpine BÖHLER sales companies. The data contained in this brochure is merely for general information and therefore shall not be binding on the company. We may be bound only through a contract explicitly stipulating such data as binding. Measurement data are laboratory values and can deviate from practical analyses. The manufacture of our products does not involve the use of substances detrimental to health or to the ozone layer.

voestalpine BÖHLER Edelstahl GmbH & Co KG

Mariazeller Straße 25 8605 Kapfenberg, AT

T. +43/50304/20-0

E. info@bohler-edelstahl.at

https://www.voestalpine.com/bohler-edelstahl/de/

